



! Pin screw for additional locking of the fiber ferrule:
- before pulling the FC-APC-connector:
unlock the pin screw.
-before inserting the FC-APC-connector:
make sure the ferrule receptacle is not blocked by the pin screw !

! Don't touch other screws !

Allgemeintoleranz ISO 2768 - f		Maßstab: 1:1	
60FC-Q-4-F90x30-xx		Fiber Collimator	
60FC-Q-4-F90x30-xx		8902-4110-0506	
Schäfer&Kirchhoff OPTO-SENSORIK UND MESSTECHNIK		Blatt A2	
Datei: 980241100506.idw		Blatt: 2	