

## 5LPM40-S150-1+55CM-450-44-O06-A7.5-P-6

Macro Line Generator with a large fan angle




### FEATURES

Laser line with a large fan angle, Gaussian intensity distribution and extended depth of focus.

- Line length: 101 mm
- Line width: 99  $\mu\text{m}$
- Wavelength: 450 nm
- Working distance: 142 mm
- Depth of focus: 45.1 mm

- Macro Line Generator for extended depth of focus



## DESCRIPTION

The laser diode beam source type 5LPM40-S150-1+55CM-450-44-O06-A7.5-P-6 has a fan angle of 40° and an extended depth of focus.

The intensity profile is Gaussian in line direction clipped by an aperture with an edge intensity of 15 %. The line width is constant along the laser line. Across the laser line the intensity distribution is approx. Gaussian.

The laser has integrated electronics [type P](#) with micro-controller for control of the laser output power. The output power can be controlled using the [modulation input ports \(TTL and analog\)](#) or manually using the potentiometer.

The working distance can be adjusted by adjusting the focus setting. Please note that beam parameters like line length and line width increase proportionally to the working distance. A fine-adjustment of the distance between laser and target is recommended for fine-focusing.

## TECHNICAL DATA

5LPM40-S150-1+55CM-450-44-O06-A7.5-P-6

Series	5LPM	
Order Code	5LPM40-S150-1+55CM-450-44-O06-A7.5-P-6	
Line profile	Gaussian Intensity Distribution	
Line type	Laser Macro Line	
Wavelength	450 +10/-10 nm	
Laser output power	44 mW	
Laser safety class	3B	
Fan angle $\alpha$	40 deg	
Focussing range	120-255 mm	
Working distance	142 mm	
Line length	101 mm	
Line width	0.099 mm	
Depth of focus	45.1 mm	
Edge intensity	15 %	
Diameter laser module	25/28 mm	
Module length	95.5 mm	
Installation length	267.5 mm	
Cable length	1.5 m	
Connector type	Lumberg SV50 IEC 61076-2-106	
Supply voltage	5 $\pm$ 0.2 V	
Max. current consumption	0.5 A	
Working temperature	15 - 40 °C	
Modulation inputs	Analog	TTL
Input resistance	9 kOhm	9 kOhm
Max. modulation frequency	0.01 kHz	250 kHz
Modulation delay ON/OFF	3000/3000 $\mu$ s	0.5/0.2 $\mu$ s
Rise / Fall time	40000/40000 $\mu$ s	0.5/0.5 $\mu$ s

## ACCESSORIES

50HD-15

Hex key WS 1.5

9D-12	Screwdriver WS 1.2
13MK-25-36-10-F	Mounting Console with flat base plate
13MK-25-36-10-M	Mounting Console with base plate with dovetail profile
PS051003E	Power Supply 5 V

## RELATED PRODUCTS

### LASER MODULES SERIES 5LPM

- Macro Line, **large** fan angle
- Gaussian intensity distribution
- Extended depth of focus

### LASER MODULES SERIES LNC-5LPM

- Macro Line, **large** fan angle
- Gaussian intensity distribution
- Extended depth of focus
- Low noise

### LASER MODULES SERIES 13LRM

- Macro Line Generator, fan angle
- Uniform intensity distribution
- Extended depth of focus

### LASER MODULES SERIES 13LNM

- Micro Line Generator, **small** fan angle
- Uniform intensity distribution
- Extended depth of focus

### LASER MODULES SERIES 5LMM+25CM

- **Compact** Micro Line, **small** fan angle
- Gaussian intensity distribution
- Extended depth of focus

### LASER MODULES SERIES 5LPM+25CM

- **Compact** Macro Line, **large** fan angle
- Gaussian intensity distribution
- Extended depth of focus

This is a printout of the page [https://sukhamburg.com/products/details/5LPM40-S150-1\\_55CM-450-44-O06-A7\\_5-P-6](https://sukhamburg.com/products/details/5LPM40-S150-1_55CM-450-44-O06-A7_5-P-6) from 4/25/2024

## CONTACT

For more information please contact:

**Schäfter + Kirchhoff GmbH**

**Kieler Str. 212**

**22525 Hamburg**

**Germany**

**Tel: +49 40 85 39 97-0**

**Fax: +49 40 85 39 97-79**

**[info@sukhamburg.de](mailto:info@sukhamburg.de)**

**[www.sukhamburg.com](http://www.sukhamburg.com)**

## LEGAL NOTICE

**Copyright 2020 Schäfter+Kirchhoff GmbH. All rights reserved.**

Text, image, graphic, sound, video and animation files and their arrangement on Schäfter+Kirchhoff GmbH webpages are protected by copyright and other protective laws. The content may not be copied for commercial use or reproduced, modified or used on other websites. [\[more\]](#)