5LTM-75-22+55CM-635-5-H10-A8-C-6


Semi-telecentric Macro Line Generator



FEATURES

Semi-telecentric laser line with constant line length of 2.4 mm and extended depth of focus.

- Line length: 2.4 mm
- Line width: 40 μm
- Wavelength: 635 nm
- Working distance: 68 mm
- Depth of focus: 3.98 mm
- Macro Line Generator for extended depth of focus



DESCRIPTION

The laser diode beam source type 5LTM-75-22+55CM-635-5-H10-A8-C-6 produces a semi-telecentric laser line with 2.4 mm line length. In this case the line length is given on the 13.5%-level. The intensity profile is Gaussian in line direction and the line is truncated at 4.8 mm. The line width is constant along the laser line. Across the laser line the intensity distribution is approx. Gaussian.

The laser has integrated electronics <u>type C</u> for control of the laser output power. The output power can be controlled using the <u>modulation input ports (TTL and analog)</u> or manually using the potentiometer.

For this laser type the working distance is fixed. A fine-adjustment of the distance between laser and target is recommended for fine-focusing in order to achieve minimal line width.



TECHNICAL DATA

5LTM-75-22+55CM-635-5-H10-A8-C-6

Series		5LTM
Order Code	5LTM-75-22+55CM-635-5-H10-A8-C-6	
Line profile	Gaussian Intensity Distribution	
Line type	Laser Macro Line	
Wavelength	635 +10/-10 nm	
Laser output power	5 mW	
Laser safety class	3R	
Focussing range	68-68 mm	
Working distance	68 mm	
Line length	2.4 mm	
Line width	0.04 mm	
Depth of focus	3.98 mm	
Edge intensity	33 %	
Diameter laser module	25/28 mm	
Module length	78.5 mm	
Installation length	176.5 mm	
Cable length	1.5 m	
Connector type	Lumberg SV50 IEC 61076-2-106	
Supply voltage	5 ± 0.2 V	
Max. current consumption	0.25A	
Working temperature	0 - 40 °C	
Modulation inputs	Analog	TTL
Input resistance	22 kOhm	22 kOhm
Max. modulation frequency	100 kHz	100 kHz
Modulation delay ON/OFF	1/0.5 µs	2/1 μs
Rise / Fall time	3/2 µs	3/2 µs

ACCESSORIES

9D-12

Screwdriver WS 1.2

13MK-25-36-10-F

Mounting Console with flat base plate



13MK-25-36-10-M	Mounting Console with base plate with dovetail profile	
PS051003E	Power Supply 5 V	
RELATED PRODUCTS		
LASER MODULES SERIES 5LT-2	 Semi-telecentric Micro Line Gaussian intensity distribution Constant line length ca. 2 mm 	
LASER MODULES SERIES LNC-5LTM-2	 Semi-telecentric Macro Line Gaussian intensity distribution Constant line length ca. 2 mm Extended depth of focus Low noise 	
LASER MODULES SERIES 13LTM	 Semi-telecentric Macro Line Uniform intensity distribution Constant line length 15 mm Extended depth of focus 	
LASER MODULES SERIES 5LTM-1+25CM	 Compact semi-telecentric Macro Line Gaussian intensity distribution Constant line length ca. 4.8 mm Extended depth of focus 	
LASER MODULES SERIES 5LTM-1	 Semi-telecentric Macro Line Gaussian intensity distribution Constant line length ca. 4.8 mm Extended depth of focus 	
LASER MODULES SERIES 5LTM-2+25CM	 Compact semi-telecentric Macro Line Gaussian intensity distribution Constant line length ca. 2 mm Extended depth of focus 	



DATA SHEET

This is a printout of the page <u>https://sukhamburg.com/products/details/5LTM-75-22_55CM-635-5-H10-A8-C-6</u> from 5/6/2024

CONTACT

For more information please contact: Schäfter + Kirchhoff GmbH Kieler Str. 212 22525 Hamburg Germany Tel: +49 40 85 39 97-0 Fax: +49 40 85 39 97-79

info@sukhamburg.de www.sukhamburg.com

LEGAL NOTICE

Copyright 2020 Schäfter+Kirchhoff GmbH. All rights reserved.

Text, image, graphic, sound, video and animation files and their arrangement on Schäfter+Kirchhoff GmbH webpages are protected by copyright and other protective laws. The content may not be copied for commercial use or reproduced, modified or used on other websites. [more]

